

STAIRLIFT  
FOR STRAIGHT  
AND CURVED  
STAIRCASES

# FLOW TWO

ACCESS



**THE FLOW2 SINGLE  
RAIL STAIRLIFT  
IS THE MARKET  
LEADER WHEN IT  
COMES TO CURVED  
STAIRLIFTS AND IS  
THE SMARTEST LIFT  
OF ITS TYPE.**

**02**

The award-winning Flow2 stairlift can be truly considered one of the world's leading stairlifts. The Flow2 is fitted onto your staircase and not your wall allowing the lift to be installed quickly, easily and with minimal disruption to your home.



“

I'm really pleased and very happy with the style of my Flow2 stairlift. I'm over the moon that I don't have to walk up and down the stairs anymore, I'm over the moon with the whole thing.”

**1**

## IT'S ALL ABOUT YOU

Designed with you in mind, the Flow2 has an ergonomically-shaped seat which provides you with an enjoyable and comfortable ride. The Flow2 is available in a number of finishes and colour options that allow you to match it to the style of your home. Choose from fabric, vinyl and leather seat covers and a range of different rail colours.

**3****2**

## COMPACT AND DISCREET

**04**

When not in use the Flow2 is folded away to only 340mm on any landing, out of the way of other staircase users. The Flow2 has a single discreet rail that closely follows the line of your stairs and can be fitted on either side of your staircase.

**3**

## SAFETY

Your safety is of paramount importance to us. The Flow2 stairlift is certified to machine directive 2006/42/EG and BS EN 81-40. The seat is adjusted in height so you can get on and off safely at the top or bottom landing. During travel the seat belt and optional wrap-around armrests keep you secure on the stairlift. If the Flow2 encounters an obstacle during travel, it will safely come to a stop. The stairlift is battery operated, which means you can still use it during a power cut.

**2**

Manufactured using the very latest technology, the Flow2 can be installed on nearly any type of staircase. The automatic swivel and levelling technology (ASL) allows the Flow2 to be fitted on staircases as narrow as 610 mm. This feature, unique to the Flow2, enables your stairlift to turn while in motion, making it one of the most adaptable stairlifts in the world.



1

05



**ASL**

ADVANCED

06 SWIVEL AND

LEVELLING

TECHNOLOGY

ASL technology enables the Flow2 stairlift to rotate and stay perfectly level while in motion. By rotating during travel, you're always in the safest and most comfortable position.



**1**

**The seat is always in the correct position to get on and off safely**

The Flow2 swivels as it travels, this means that getting on and off the lift at either end of the staircase is quick and easy. At the top of the staircase the seat can rotate away from the open staircase, allowing a safe exit from the seat.

**2**

**Constantly working to save you time and provide safety and comfort**

ASL technology operates while the lift is moving. Therefore you avoid additional stops and swivel movements at the beginning, during and at the end of the ride. This saves time and provides additional safety and comfort. The lift really moves in one "Flow".

**3**

**Internal or external rail on the narrowest and steepest stairs**

Even in cases where the staircase is narrow and steep, the Flow2 can be installed closer to the step and on either side of the staircase. Your stairlift will be less obtrusive and your staircase remains accessible for other family members in your home.

**4**

**Unique technology that can only be found with the Flow2**

Your well-being is important to us – when you choose ASL technology the footrest swivels with the seat ensuring your legs and feet remain in a natural and comfortable position, relieving any additional strain on your joints.



**ASL TECHNOLOGY  
ALLOWS THE RAIL  
TO BE KEPT AS  
LOW AS 62MM ON  
A WIDE VARIETY  
OF STAIRCASE  
STYLES AND  
CONFIGURATIONS.**

09



# OPTIONS

10

IT'S ALL  
ABOUT YOU

When you choose the Flow2 stairlift, you ensure the best fit for your staircase. With a single discreet rail, this stairlift can be tailor-made to fit any staircase.

# RAIL



## Standard Drop Nose

The standard drop nose is the perfect solution if there is an obstruction such as a door near to the bottom of the stairs. The drop nose requires just 175 mm of space from the bottom step.




## Vertical 'Short-Start' Drop Nose

Where space is even tighter at the bottom the 'short-start' drop nose can be installed, needing only 100 mm of space from the bottom step.



## Horizontal Overrun

Where you have extra space at the bottom of the stairs the horizontal overrun allows the chair to be parked away from the bottom step.




## Parking Curve


A parking curve allows the chair to be parked neatly out of the way of the stairs.

11


# COLOUR



Grey



White/Grey



Beige/Brown




Brown/Grey

# UPHOLSTERY

## Vinyl



Red



Grey



Maroon



Sisal

## Fabric



Dark Brown



Beige



Red

12

## Elegant Leather



Aubergine-Beige



Beige-Grey




Brown-Beige



Brown-Cognac



Brown-Grey



Red-Beige


## Deluxe Leather



Beige



Dark Brown



Dark Red

## ARMREST



Straight



Curved

13

## JOYSTICK & CALLPARK



JoyStick



Callpark

USING A SERIES OF  
BESPOKE CURVES  
AND 180° BENDS,  
THE FLOW2 RAIL  
CAN BE INSTALLED  
ON MULTIPLE  
FLOORS UP TO A  
TOTAL RAIL LENGTH  
OF 34M.

14

3 4 M

**RAIL**

180°

# BENDS



COFFEE LIVING  
AMERICAN FASHION  
ECO HOUSES  
THE RITZ-CARLTON HOTEL

CARS  
THE PATRICK BOOK  
THE WALKER STORY TELLER



Finnish Architecture with an Edge  
KAWA MOSE  
THE WALKER STORY TELLER

THE FLOW2  
STAIRLIFT CAN  
BE INSTALLED  
ON STAIRCASES  
AS NARROW AS  
610MM AND AS  
STEEP AS 70°.




# TECHNICAL SPECIFICATION CERTIFIED TO THE HIGHEST STANDARDS

18



# SPECIFICATION

Speed	Max 0.15 m/s
Drive Type	Rack and pinion
Motor Wattage	350 W – Drive Motor 350 W – Horizontal Motor
Weight Capacity	125 kg
Batteries	2 × 12 V batteries; total 24V
Operation	Joystick control as standard
Staircase Incline	Up to 70°
Certification	Machine Directive 2006/42/EG BS EN 81-40
Automatic Stop	Yes
Footrest	Yes
Retractable Safety Belt	Yes



The Flow2 stairlift is one of the most reliable products I've had the pleasure of working with."



HARCHICIA QUE  
PREMPOR EPUDAEP  
UDICTE NATUM  
QUODIS QUE  
VOLLAB ILIATIS  
AD MAGNAM.



# OUR

# LOCATIONS

22



Our head office is in Stockton-on-Tees, in North East England, one of the most dynamic and globally-focused regions of the United Kingdom. We also have sales offices in Dubai and Singapore as well as a number of regional sales and technical staff located across Europe.



Access BDD is one of Europe's leading suppliers of stairlifts, platform lifts and home lift solutions.

Your local Access BDD dealer is:

